

11098-538 PSU 19" AC/DC FOR COMPACTPCI SERIAL, 3 U, 8 HP, 300 W



KEY FEATURES

19" pluggable PSU for CompactPCI Serial applications
Active power factor correction and active current-share function
N+1 redundancy, hot swap
Output signaling: PS present, power failure, PS_ON and enable
I2C interface

PRODUCT ATTRIBUTES

High efficiency, > 90% at 220 VAC

Product Type: Power Supply
Type: 19" Switched-Mode
Works With: CompactPCI Serial Systems
Input Voltage AC: 90 – 264 V
Power: 300 W
Number of Output Voltages: 2
Voltage 1: 12 V
Current 1: 25 A
Voltage 2: 5 V
Current 2: 2.5 A
Rack Height: 3 U
Rack Width: 8 HP

ADDITIONAL PRODUCT DETAILS

Pluggable 19" Power Supply, for CompactPCI applications. The Power Supply has a wide range AC input, a 12V DC Payoald and +5 V DC Standby output.

CERTIFICATIONS





North America

All locations +1.763.422.2661 Chat with us: schroff.nvent.com

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: schroff.nvent.com

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: schroff.nvent.com

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: schroff.nvent.com



© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

Our powerful portfolio of brands:

nVent reserves the right to change specifications without notice.