

**7/8" male 0° / 7/8" female 0°**

PUR 5x1.5 gy UL/CSA+drag chain 15m

Male straight to female straight

7/8" - 7/8"




Power cable


5-pole

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Form

50021

### Technical Data

|                               |   |
|-------------------------------|---|
| Operating voltage             | max. 230/400 V AC/DC  |
| Operating current per contact | max. 12 A   |
| Locking of ports              | Screw thread 7/8" (recommended torque 1.5 Nm) self-securing |
| Protection                    | IP67 inserted and tightened (EN 60529)                      |

### Cables

|                             |                                |
|-----------------------------|--------------------------------|
| Cable number                | 961                            |
| No./diameter of wires       | 5 × 1.5 mm <sup>2</sup>        |
| Wire isolation              | PP (br, wh, bl, bk, gnye, num) |
| C-track properties          | 5 Mio.                         |
| Torsion                     | 2 Mio. ± 180°/m                |
| Jacket Color                | gray                           |
| Shore hardness outer jacket | 90 ± 5A                        |
| Material (jacket)           | PUR (UL/CSA)                   |
| Outer diameter              | approx. 8.7 mm                 |
| Bend radius (fixed)         | 7.5 × outer Ø                  |
| Bend radius (moving)        | 10 × outer Ø                   |
| Temperature range (fixed)   | -50...+80 °C                   |
| Temperature range (mobile)  | -20...+80 °C                   |

### Commercial data

|                   |    |
|-------------------|----|
| country of origin | CZ |
|-------------------|----|

|                        |          |
|------------------------|----------|
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |

---