



IWLAN RCOAX N-CONNECT FEMALE POWER SPLITTER 2-FOLD
2.4 AND 5 GHz Y-ELEMENT FOR SPLITTING THE RCOAX CABLE

Electrical data

Number of electrical connections	3
Type of electrical connection	N-Connect female
Transmission frequency	2.4 ... 6 GHz
Impedance	50 Ω
Return loss / minimum	24 dB
Insertion loss / maximum	3.05 dB

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation 	-25 ... +110 °C
<ul style="list-style-type: none"> during storage 	-25 ... +110 °C
<ul style="list-style-type: none"> during transport 	-25 ... +110 °C
Protection class IP	IP 67

Design, dimensions and weight

Width	71.4 mm
Depth	34 mm
Length	131.4 mm
Net weight	937 g

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes

Further Information / Internet Links

Internet-Link	
---------------	--

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

last modified:

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

09.03.2015