


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2092090002](#)
Status: **Active**
Overview: [L1NK Connector System](#)
Description: L1NK 300 Receptacle Housing, Single Row, 2 Circuits, UL 94V-0, Black

Documents:

3D Model	Packaging Specification 2092090000-PK-000 (PDF)
3D Model (PDF)	Test Summary 2092080000-TS-000 (PDF)
Drawing (PDF)	Datasheet (PDF)
Product Specification 2092080000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 2092080000-AS-000 (PDF)	



General

Product Family	Crimp Housings
Series	209209
Application	Power, Wire-to-Board
Overview	L1NK Connector System
Product Name	L1NK 300
UPC	193264185689

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.281/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	2092080000-AS-000
Packaging Specification	2092090000-PK-000
Product Specification	2092080000-PS-000
Sales Drawing	2092090000-SD-000
Test Summary	2092080000-TS-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[209209](#) Series

Mates With

L1NK 300 Header [2092080002](#)

Use With

L1NK 300 Female Terminal [2063960001](#) ,
L1NK 300 TPA Retainer [2093250002](#)