


### BU-1420701201 (50 Ohm Straight Jack Receptacle)



#### (Dimensions in Inches)

- Impedance: 50 Ohms
- Frequency Range: 0-18G
- Working Voltage: 335V at Sea Level
- Dielectric Withstanding Voltage: 1000V min at sea level
- Contact resistance: 3 milliohms
- Mating Torque: 7-10 Inch Pounds
- Material:
  - Body – Gold plated Brass
  - Contact – Gold plated Beryllium Copper
  - Insulator – Teflon
- Meets or Exceeds the applicable paragraph of MIL-C-39012
- Operating Temperature: -65°C (-85°F) to 150°C (302°F)
- RoHS 3 Compliant