

# Bevel Gears - Acetal




- Injection Moulded
- Select matched pairs for the stated transmission ratio
- Pressure angle 20°

Material : Acetal

Module : 1.0

Ratio : 2:1



Order Code	Teeth	Overall Dia (da)	Pitch Dia (d)	Hub Dia (ND)	Bore (B) (H7)	Torque (Ncm)	Weight (g)
102355556	15	16.8	15	12.2	5	12	2.4
102355557	30	31.1	30	18	8	24	7

Ratio: 3:1

Order Code	Teeth	Overall Dia (da)	Pitch Dia (d)	Hub Dia (ND)	Bore (B) (H7)	Torque (Ncm)	Weight (g)
102355576	15	16.6	15	12.3	5	16	2.8
102355577	45	46.1	45	23.4	10	48	17.5