

## Uni-Dicht-Verschraubung Pg 16, 6,5-9,5mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 00 000 5086
Specification	Uni-Dicht-Verschraubung Pg 16, 6,5-9,5mm
HARTING eCatalogue	<a href="https://b2b.harting.com/09000005086">https://b2b.harting.com/09000005086</a>

### Identification

Category	Accessories
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	≤10 Nm (depending on the cable and the seal insert used)
Wrench size	24
Limiting temperature	-40 ... +130 °C
Degree of protection acc. to IEC 60529	IP68
Size	Pg 16
Clamping range	6.5 ... 9.5 mm

### Material properties

Material (cable glands)	Metal
Colour (accessories)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained



**Pushing Performance**  
Since 1945

## Commercial data

Packaging size	10
Net weight	38.9 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140001671
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)