

Adjustable clamps

Depressed centre



Version:

- Heat-treated steel
- Painted
- Single depressed centre



Art. no.	26138 010
Slot width	6.6 mm
Length	60 mm
Suitable cheese-head screw DIN 912	M6
Slot length	20 mm
Clamping shoe height	10 mm
Clamping shoe width	20 mm
Height	9 mm
Width 3	10 mm
Height 2	8 mm
DIN	6316

EAN-Code

4020772071028