

Undercounter cabinet with CLIP-O-FLEX with pull-out system

Height 800 mm, including 6 CLIP-O-FLEX trays

CLIP-O-FLEX®

Application:

Thanks to the flexible and modular CLIP-O-FLEX system, the cabinet can be optimally designed and adapted to the individual work sequences in production, assembly, development, training and further education. Your work/storage area or your organisation system are fixed with one clip and at the same time with the highest level of horizontal and vertical flexibility.

Execution:

- Solidly welded steel sheet construction
- Undercounter cabinet equipped with one door, height 540 mm and 2 drawers, front height 90 mm
- With convenient pull-out system incl. 6 CLIP-O-FLEX trays with hook-in brackets 0/40/80°

Advantage:

- CLIP-O-FLEX: flexible hook-on system with only one hooking movement
- Ergonomic workplace design thanks to different inclines and can be relocated horizontally
- Quick access to work equipment, very clear overview
- Quick retrofitting, exchange and replacement
- Best mobility, less walking required



Art. no.	50237 155
Brand	CLIP-O-FLEX
Manufacturer Part Number	28347
Design	With pull-out system
Door position	Left
Number of cabinets 260 x 345 x 30 mm	6 PCS
Load-carrying capacity per shelf board	10 kg
Number of drawers	2 PCS
Drawer front height	2 x 90 mm
Drawer width (inner dimension)	365 mm
Drawer depth (inner dimension)	294 mm
Pullout type	Full extension
Load-carrying capacity per drawer	35 kg
With single pull-out safety brake	No
Height	800 mm
Width	474 mm
Depth	405 mm
With doors	Yes
Door height	540 mm
Central locking	Yes
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Gross Weight	59.000 kg
Product Group	586