

Table trolley with 2 wooden load areas

Suitable for Euronorm containers, load capacity 250 kg

Application:

For transporting Euronorm containers or as a serving trolley for small parts in production and assembly.

Execution:

- Welded angular steel frame
- Suitable for Euro crates 600 x 400 mm
- Loading surfaces made from wooden panel board, edge 10 mm
- Clear floor distance 400 mm
- Thermoplastic rubber tyres, grey, non-chalking
- Plastic rims with precision deep groove ball bearings and thread guards
- Sliding handle with soft hose casing

Advantage:

- Ideal combination of transport trolley and serving trolley
- Robust design
- Elegant HK design

Delivery:

Disassembled



Art. no.	50269 139
Brand	HK
Manufacturer Part Number	50269 139
Load-carrying capacity	250 kg
Number of loading surfaces	2
Length	675 mm
Length x width x height	675 x 415 x 635 mm
Width	415 mm
Loading surface length	605 mm
Height	635 mm
Loading-surface width	410 mm
Loading-surface height	195 mm, 625 mm
Surface	Powder-coated
Loading surface size	605 x 410 mm
Wheel diameter	125 mm
Material of wheel	TPE
Number of steering rollers	4
With wheel lock	Yes
Material of loading surface	Wood composite board
With handle	Yes
Colour	Anthracite grey RAL 7016
Gross Weight	21.000 kg
Product Group	504

EAN

4053625359196