

9011 M pneumatic impact screwdriver

square drive 3/8"



Application:

extremely compact design enables work even in restricted spaces

Execution:

- 3 power levels in clockwise rotation, 1 power level in anti-clockwise rotation
- handle insulated against cold
- Exhaust air discharged downwards through the handle

Advantage:

- low-vibration
- one-handed operation for left-handed and right-handed users

Delivery:

Includes coupling plug



Art. no.	75065 071
Brand	HAZET
Manufacturer Part Number	9011M
Model	9011M
Suitable for screw	M13
Max. tightening torque	461 Nm
Max. releasing torque	461 Nm
Max. idle speed	6500 rpm
Air consumption	85.2 l/min
Tool holding device	3/8-inch external square
Hammer mechanism system	Jumbo hammer mechanism
Length	92 mm
Connection thread	G 1/4 inch
Inner hose diameter	10 mm
Operating pressure	6.3 bar
Sound-pressure level	90.3
Weight	1.24 kg
With right/left-hand rotation	Yes
Gross Weight	1.484 kg
Product Group	738

EAN

4000896201570