

🌡️ - 30°C ... + 100°C

Inhalt

Portrait

ROHRflex  
Wellenschlauch

FLEXAquick  
Anschluss-  
technik

## Schlauchhalter mit Deckel

**Material:** verstärkter Kunststoff (PA)

- Durchgangsloch zur Befestigung mittels Schrauben
- Rippenfixierung zur Zugentlastung
- unterschiedliche Größen aneinanderreihbar
- einsetzbar in C-Profileschienen

**Optionales Zubehör:**

Verbindungssteg RQHV

## Tubing clamp with cover

**Material:** mod. reinforced Plastic (PA)

- Through hole for fastening by screws
- ribbed fixing for strain relief
- assembly of varying sizes joined in line
- for using in combination with C-profile bar

**Optional Accessories:**

connecting element RQHV



FLEXA No.	FLEXA No.	AD OD						kg/100	St. Pcs.	
grau grey	schwarz black	ø	A mm	B mm	C mm	D mm	E mm			
<b>RQHG</b>										
5030.028.007	5030.028.207	<b>10,0</b>	19,5	19,0	8,4	13,0	15,0	5,5	0,39	50
5030.028.009	5030.028.209	<b>13,0 1/4"</b>	19,5	22,6	9,3	14,5	15,0	5,5	0,42	50
5030.028.011	5030.028.211	<b>15,8 5/16"</b>	21,5	25,4	11,2	16,1	15,0	5,5	0,56	50
5030.028.013	5030.028.213	<b>18,5</b>	24,5	29,0	12,6	18,0	15,0	5,5	0,56	50
5030.028.016	5030.028.216	<b>21,2</b>	26,5	33,0	16,6	21,0	15,0	6,5	0,65	50
5030.028.021	5030.028.221	<b>28,5 3/4"</b>	34,7	39,4	20,4	22,7	15,0	6,5	0,88	25
5030.028.029	5030.028.229	<b>34,5 1"</b>	40,0	44,4	25,6	26,0	15,0	6,5	0,92	25
5030.028.036	5030.028.236	<b>42,5 1 1/4"</b>	48,5	52,9	30,1	30,0	15,0	6,5	1,28	25
5030.028.048	5030.028.248	<b>54,5 2"</b>	59,9	65,8	38,1	37,3	15,0	6,5	1,74	10



## Einteiliger Schlauchhalter

**Material:** Kunststoff (PA)

- Durchgangsloch zur Befestigung mittels Schraube
- Rippenfixierung zur Zugentlastung
- durch Filmscharnier angebundener Deckel zur schnellen Montage
- auch unterschiedliche Größen sind aneinanderreihbar
- einsetzbar in C-Profileschienen

## One-piece tubing clamp

**Material:** Plastic (PA)

- Through hole for fastening by screws
- ribbed fixing for strain relief
- quick assembly by means of a filmhinge
- assembly of varying sizes joined in line
- for using in combination with C-profile bar



FLEXA No.	FLEXA No.	AD OD						kg/100	St. Pcs.
grau grey	schwarz black	ø	A mm	B mm	C mm	E mm	ø l mm		
<b>RQS</b>									
5030.020.007	5030.020.207	<b>10,0</b>	21,7	23,7	8,0	20	4,5	0,69	50
5030.020.009	5030.020.209	<b>13,0</b>	26,0	29,0	9,00	20	5,5	0,93	50
5030.020.011	5030.020.211	<b>15,8</b>	26,0	29,0	11,0	20	5,5	0,85	50
5030.020.013	5030.020.213	<b>17,8 / 18,5</b>	32,5	37,0	12,5	20	5,5	1,20	50
5030.020.016	5030.020.216	<b>21,2</b>	32,5	37,0	16,5	20	6,5	1,20	50
5030.020.018	5030.020.218	<b>21,8</b>	32,5	37,0	16,5	20	6,5	1,20	50
5030.020.021	5030.020.221	<b>28,5</b>	43,3	50,4	20,0	20	6,5	1,70	25
5030.020.029	5030.020.229	<b>34,5</b>	43,3	50,4	25,5	20	6,5	1,70	25
5030.020.036	5030.020.236	<b>42,5</b>	65,0	77,0	30,0	20	6,5	3,20	25
5030.020.048	5030.020.248	<b>54,5</b>	65,0	77,0	38,0	20	6,5	2,90	10

