

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0430300011](#)
Status: **Active**
Overview: [Micro-Fit Connector System](#)
Description: Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 26-30 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-43030-003 \(PDF\)](#) [Product Literature \(PDF\)](#)
[Test Summary TS-43045-002-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [43030](#)
 Application Power, Wire-to-Board, Wire-to-Wire
 Crimp Quality Equipment Yes
 Overview [Micro-Fit Connector System](#)
 Packaging Alternative [430300005 \(Reel\)](#)
 Product Literature Order No 987650-5984
 Product Name Micro-Fit 3.0
 UPC 800754369350

Physical

Gender Female
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Net Weight 0.057/g
 Packaging Type Bag
 Plating min - Mating 0.381µm
 Plating min - Termination 2.540µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.27mm max.
 Wire Size AWG 26, 28, 30
 Wire Size mm² N/A

Electrical

Current - Maximum per Contact 8.5A


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification PK-43030-003
 Sales Drawing SD-43030-XXXX
 Test Summary TS-43045-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[43030 Series](#)

Use With

[43025](#) , [43645](#) Micro-Fit 3.0 Receptacle Housings, [44133](#) Micro-Fit BMI Panel Mount Receptacle Housings