

SIVACON, base, IP30, D: 500 mm, W: 400 mm, galvanized



Figure similar

Model	
Product brand name	SIVACON
Design of the product	Closed
Design of the surface	galvanized
Design of the product / EMC version	No
Protection class IP	IP30
Product component	
• ventilation	No
Mechanical Design	
Width	400 mm
Depth	500 mm
Net weight	2 000 g
Equipment marking	
• acc. to DIN EN 61346-2	U
• acc. to DIN EN 81346-2	UC

EMC	Declaration of Conformity	Test Certificates	other
Miscellaneous	 EG-Konf.	Special Test Certificate	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1045-2UB22-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1045-2UB22-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1045-2UB22-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



