

Glass Fiber-Optic Cable

Reflex Mode for P1XF

FL3402

Part Number



Technical Data

Optical Data

Fiber Bundle Diameter	3 mm
Working Distance	100 mm
Light Spot Diameter	10 mm
Fiber	Step Index
Fiber Distribution	statistical mixture

Mechanical Data

Temperature Range	0...60 °C
Bending Radius	50 mm
Fiber-Optic Length	0,5 m
Jacket Material	CuZn, nickel-plated

Fiber-Optic Cable Adapter No.

01

- Compatible with the P1XF001 6-channel Multispectral Sensor
- Laid out for tight installation spaces
- Rugged design

In the scanning mode, the glass fiber-optic cables are compatible with the P1XF001 6-channel Multispectral Sensor. They're ideal for use in difficult to access locations and they detect colored objects.



