



**CT3185: Convenient 10 piece MiniPro Test Clip lead kit**



Type	10 pc Kit
IEC Rating	33 Vac / 70 Vdc
Voltage Max	150 V
Current Max	6 A
Length	50 cm
Jacket Material	PVC
Conductor Area	0.40 mm <sup>2</sup>
Wire Gauge	21 AWG
Stranding (# x Ø)	104 x 0.07 mm
Wire OD	2.0 mm (0.079")
Temperature	-20 to +80° C
RoHS (2011/65/EU)	Compliant
Yes	

