

# PANEL MOUNT INDICATOR, NON-RELAMPABLE

## NEON TECHNOLOGY

MOUNTING HOLE, Ø 0.380"

PART NO.	LENS COLOR	VOLTAGE	CURRENT [mA]	RATED LIFE HOURS
<b>NEON 115VAC SERIES</b>				
WL-6010M1	RED	105-125VAC	1.5mA	25,000
WL-6010M3	AMBER	105-125VAC	1.5mA	25,000
WL-6012M5	GREEN	105-125VAC	1.5mA	25,000
<b>NEON 230VAC SERIES</b>				
WL-6011M1	RED	208-250VAC	1.5mA	25,000
WL-6011M3	AMBER	208-250VAC	1.5mA	25,000
WL-6013M5	GREEN	208-250VAC	1.5mA	25,000

## NOTES


1. Recommended panel thickness  
0.030" to 0.250"
2. 6" leads with 1/2" strip are standard
3. Storage temperature  
 $T_{STG}$ : -25°C - +100°C
4. Ambient temperature  
 $T_A$ : -20°C - +100°C
5. Voltage tolerance  
 $V_{OP}$ : ±10%
6. Body material  
Nylon, white
7. Lens material  
Polycarbonate
8. Bezel material  
Stainless steel
9. Wire gauge  
18 AWG
10. Gaskets  
Buna-N
11. Mounting hardware (nut, lock washer, and gasket) included

## CERTIFICATIONS

UL (E340667), RoHS



## DIMENSIONAL CHARACTERISTICS



unless otherwise specified, all dimensions are in inches



## OPTIONS

Additional options and lens styles available. Please contact Wamco for more information.

