



CT2900A: UL listed probe set with 2 mm (0.080") diameter probe tip. Connector is a right-angle sheathed 4 mm banana plug. Alligator clip pair featuring gold plated pin tip sockets



Description:

UL listed DMM probe set with 2 mm (0.080") diameter probe tip. Connector is a right-angle sheathed 4 mm banana plug. Set includes alligator clip pair featuring gold plated pin tip sockets. They mate easily onto the probe tips.

- Materials: Body: PVC/Nylon; Contact: Brass, Nickel Plt.
- Banana Contact: Phosphor Bronze, Nickel Plt.
- Alligator Clips: Steel, Nickel Plt.

SPECIFICATIONS:

IEC Rating	1,000 V CAT III
Current Max	12 A
Resistance Max	30 mohm
Jacket Material	PVC
Conductor Area, mm ²	0.75
Wire Gauge, AWG	18
Stranding, # x mm	195 x 0.07
OD, mm (in)	3.7mm (0.146")
Temperature	-20 to +80 degC
RoHS (2011/65/EU)	Pending