




Material: Messing vernickelt  
 max. Betriebsdruck: 18 bar  
 max. Betriebstemperatur: 200 °C  
 verwendbare Schläuche: PA, PE, PU



13.714-8-E

### Winkelaufschraubverschraubung

Typen Nr.	Artikel Nr.	ØD	A	B	C	L	 1	 2	O-Ring
13.718-6-E	115237	6/4	G 1/8	8,0	19,0	22,5	12	10	ohne
13.714-6-E	115235	6/4	G 1/4	10,5	23,0	25,0	12	11	ohne
13.714-8-E	115236	8/6	G 1/4	10,5	23,0	25,0	14	11	ohne
13.714-10-E	115234	10/8	G 1/4	11,0	23,5	26,0	16	13	ohne