



FCXX*1)S0G1

e.g. FC25S0G1

RoHS compliant

*1) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.4	25
15	39.1	24.7	33.3
25	53	38.5	47.04
37	69.3	54.9	63.5

No.	St.	Type	Description/Material
4	xx	Signal contact	S36 / Brass / AWG 20
3	1	Shell	Steel
2	1	Sealing compound	Epoxy resin (-55°C - +85°C)
1	1	Insulator	Plastic

No.		St.	Type	Description/Material
				Surface plating/Colour/Class
				0.3µm Au / C-Filter 1nF -20/+80%
				fin plated
				black
				black

ISO 2768-m	SCALE	TITLE
NAME / DATE	2:1	D-Sub Filter-Connector
19-10-2009		
DRAWN		
CHECKED		

REV.	DATE	CH.-NO.	DWG.NO.	REPLACEMENT FOR:	PAGES
2	10-12-2009	2221 6	FCXXS0G1	FCXXS0G1	1
1					2

