



Datenblatt - Fiche technique - Data sheet

**11.04.5636**




ROLINE DisplayPort Kabel, DP ST - Mini DP ST, 3,0m

ROLINE Câble DisplayPort DP M - Mini DP M, 3,0m


ROLINE DisplayPort Cable, DP - Mini DP, M/M, 3 m

# ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE
△K2	B	ECR # 110829-7 EDIT: CABLE SPEC, TITLE	08/29/11'



- NOTE:
- CABLE:UL20276 [32(7/0.08T.C)]x1P INS:FOAM-SKIN-PE+D.W(7/0.08T.C)  
 +Free-edge-al-foil/Mylar|x5C+#32(7/0.08T.C)x5C INS: PP+AL/MY  
 +B.D(85%)PVC JACKET; OD:5.5±0.2mm COLOR:BLACK(NK-K01).
  - CONNECTOR:  
 P1:DISPLAYPORT 20P MALE W/P/CB CONTACT:15u",SHELL:NI-PLATED.  
 P2:MINI DISPLAYPORT 20P MALE CONTACT:15u",SHELL:NI-PLATED.
  - SHIELD: P1:INNER MOLD MUST BE WRAPPED COPPER TO CONNECTOR SHELL & CABLE BRAID  
 P2:COPPER-FOIL 360° SOLDERED TO CONNECTOR SHELL & CABLE BRAID
  - HOOD:P1:ASS'Y TYPE, COLOR:BLACK(NK-K01)  
 P2:MOLDED TYPE, PVC 45P, COLOR:BLACK(NK-K01)
  - ELECTRICAL TEST:  
 <1>-100% OPEN SHORT & MIS WIRE TEST.  
 <2>-CONTACT RESISTANCE 3 Ohms MAX.  
 <3>-INSULATION RESISTANCE 10M Ohms MIN.
  - PACKING: EACH PC / POLYBAG+BIG HEADER CARD+BAR CODE LABEL.



1. Tolerance Inch M/M
- |      |      |     |
|------|------|-----|
| X    | .015 | .30 |
| .XX  | .010 | .10 |
| .XXX | .005 | .05 |
- Draw  
 FANNIE 08/29/11'

**Rotronic Co., LTD.**

Title  
 DisplayPort - Mini DisplayPort Cable(V1.2)

Customer P/N

200-1447-3	11.04.5637-10	5000	50	10	20
200-1447-2	11.04.5636-20	3000	30	20	40
200-1447-1	11.04.5635-20	2000	30	20	40
DWG	P/N	L (mm)	T (mm)	PCS/INNER CARTON	PCS/CARTON

App'd	Customer: T-RAG
Scale NONE	Units M/M
Dwg No. 200-1447	REV: B
Third Angle Projection	Sheet 1/1