

Product data sheet

Item No. 92.232.1063.1

Cable assembly GST18I3K1B- 15H 10SW

geis® Connection cable female - free end; length: 1m; type GST18I3; 3-pole; 250 V / 16 A; colour of coding: black with black strain-relief; cable: H05Z1Z1-F 3G1,5, colour: black



Item No.	92.232.1063.1
EAN	4015573664661
Order Unit	75 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	1.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	S05Z1Z1-F

Cable colour	Black
Cable diameter	8 mm
Version of cable	Female - free end
Type of cord set	Connection cable
Version cable end 1	GST18i3 socket
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	Yes
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	1 m
--------------	-----

Technical drawing

Kabel/cable: H05Z1Z1-F3G1,5 halogenfrei/halogen-free
 Farbe/colour: siehe Tabelle/see table

.F	Farbe colour	Codierung *X* Buchse female	Kabelfarbe cable colour
.1	schwarz black	N @ L	schwarz black
.2	weiß white	N @ L	weiß white
.3	grau grey	N @ L	schwarz black
.5	rot red	N @ L	schwarz black

Typ/type: GST1813K1B- 15H.. SW = schwarz/black
 WS = weiß/white
 GR01 = grau/grey
 RT03 = rot/red

Teile-Nr. part-no.	L	Beispiel (Farbe: schwarz) example (colour: black)	Typ type
92.232.XX63.F	XX in dm-Schritten	92.232.1063.1 = 10dm/L= 1000mm	GST1813K1B- 15H 10SW
U2.232.XX63.F	XX in m-Schritten	U2.232.1263.1 = 12 m/L=12000mm	GST1813K1B- 15H X12SW
92.232.XX83.F	XX in dm-Schritten	92.232.1083.1 = 10dm/L= 1000mm	

83.F = spezielle Verpackung und Etikettierung nach A 1960.000
 special packaging and lable according to A 1960.000

Material: Werkstoff/Material: ZN06, 30.01, 30.02, 30.03, 30.04, 30.05, 30.06, 30.07, 30.08, 30.09, 30.10, 30.11, 30.12, 30.13, 30.14, 30.15, 30.16, 30.17, 30.18, 30.19, 30.20, 30.21, 30.22, 30.23, 30.24, 30.25, 30.26, 30.27, 30.28, 30.29, 30.30, 30.31, 30.32, 30.33, 30.34, 30.35, 30.36, 30.37, 30.38, 30.39, 30.40, 30.41, 30.42, 30.43, 30.44, 30.45, 30.46, 30.47, 30.48, 30.49, 30.50, 30.51, 30.52, 30.53, 30.54, 30.55, 30.56, 30.57, 30.58, 30.59, 30.60, 30.61, 30.62, 30.63, 30.64, 30.65, 30.66, 30.67, 30.68, 30.69, 30.70, 30.71, 30.72, 30.73, 30.74, 30.75, 30.76, 30.77, 30.78, 30.79, 30.80, 30.81, 30.82, 30.83, 30.84, 30.85, 30.86, 30.87, 30.88, 30.89, 30.90, 30.91, 30.92, 30.93, 30.94, 30.95, 30.96, 30.97, 30.98, 30.99, 30.100

Further data see catalog
 further data see catalog

PRE-ASSEMBLED CABLE
 KONFEKT LEITUNG
 Buchse/female - freies Ende/free end 1,5mm
 crimping KIT 250V halogen-free