

## collet chuck DIN 6343 173 E, hexagonal

**ORION®**

### Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- Concentricity
- $\varnothing$  1-10 mm  $\leq$  20  $\mu$ m
- $\varnothing$  11-30 mm  $\leq$  30  $\mu$ m
- $\varnothing$  31-60 mm  $\leq$  40  $\mu$ m
- Other designs and complete sets can be supplied on request.



|                                 |                    |
|---------------------------------|--------------------|
| <b>Art. no.</b>                 | <b>23353 570</b>   |
| <b>Brand</b>                    | ORION              |
| <b>Manufacturer Part Number</b> | 23353570           |
| <b>Outer diameter</b>           | 60 mm              |
| <b>Diameter</b>                 | 48 mm              |
| <b>Length</b>                   | 94 mm              |
| <b>Width across flats</b>       | 7 mm               |
| <b>Profile shape</b>            | Hexagon and smooth |
| <b>DIN</b>                      | 173                |
| <b>Diameter 2</b>               | 48 mm              |
| <b>Gross Weight</b>             | 0.670 kg           |
| <b>Product Group</b>            | 2AE                |

### EAN

4053625355785