

## electronic pocket vernier calipers

angled internal/external measuring surfaces, knife-edge callipers

Mitutoyo

### Application:

For carrying out internal measurements, measuring wall thickness in holes, carrying out measurements within a groove

### Execution:

- Digimatic
- IP67
- AUTO OFF
- ABSOLUTE system for reliable measurement
- High-contrast display

### Advantage:

- Suitable for special or difficult to reach measuring points

### Delivery:

Delivered in box



|   |  |
|---|--|
| <b>Art. no.</b>                                   | <b>32018 096</b>   |
| <b>Brand</b>                                      | MITUTOYO   |
| <b>Manufacturer Part Number</b>                   | 573-745-20   |
| <b>Min./max. length measuring range in inches</b> | 0.404-6 in   |
| <b>Data transmission type</b>                     | DIGIMATIC  |
| <b>Depth gauge rod</b>                            | Without  |
| <b>IP protection class</b>                        | IP 67  |
| <b>With drive wheel</b>                           | Yes  |
| <b>Error limit</b>                                | 0.002 in   |
| <b>Length of jaw</b>                              | 35 mm  |
| <b>Design</b>                                     | Metric, Imperial   |
| <b>Digit height</b>                               | 9 mm   |
| <b>Digit increment</b>                            | 0.01 mm  |
| <b>Digit increment in inches</b>                  | 0.0005 in  |
| <b>Type of locating</b>                           | With locking screw   |
| <b>With mm / inch switching</b>                   | Yes  |
| <b>Length</b>                                     | 233 mm   |
| <b>With automatic shut off</b>                    | Yes  |
| <b>Battery designation</b>                        | 1,5 V SR44   |
| <b>Number of rechargeable batteries/batteries</b> | 1 PCS  |
| <b>Weight of rechargeable battery/battery</b>     | 0.002 kg   |
| <b>Battery voltage</b>                            | 1.55 V   |
| <b>Type of rechargeable battery/battery</b>       | Silver oxide   |
| <b>Calibration Group</b>                          | A  |
| <b>ISO</b>  | 13385-1  |
| <b>Functions</b>                                  | Absolute function, ABS function, Origin (Dimension preset), Automatic switch-off, On/Off, With mm / inch switching |
| <b>Gross Weight</b>                               | 0.404 kg   |
| <b>Product Group</b>                              | 3MA  |

### EAN

4946368726953