

Electronic levels NIVELTRONIC

With 1 level measuring surface



Application:

For adjustment of horizontal machine beds and for checking the planarity of machine tables and guide surfaces.

Execution:

- Cast steel housing
- Battery operation (4x 1.5 V micro type AA)
- Displays in mm/m and angular seconds
- Flat base and recesses for mounting hard stone bases no. 38460
- Inductive measuring system
- With 1 level measuring surface

Delivery:

In wooden box



Art. no.	38455 010
Brand	TESA
Manufacturer Part Number	03 130063
Length	150 mm
Height	210 mm
Measuring range 1, level (+/-)	0.75 mm/m
Measuring range 2, level (+/-)	0.15 mm/m
Scale value	0.05 mm
Spirit level error limit	0.005 mm/m
Repetition accuracy, spirit level	0.001 mm/m
Gross Weight	6.314 kg
Product Group	366

EAN

7630041112238