

Ultrasonic wall thickness gauge

Includes 5 MHz 1/4" dual element measuring head

elcometer

Application:

For non-destructive recording of material thickness, for use on steel materials only. Ideal for monitoring corrosion and erosion on closed components and structures or those accessible only from one side, e.g. pipes, tanks, large metal sheets etc.

Execution:

- Robust ABS plastic housing
- Large, easy-to-read 2.4" colour display
- IP 54 degree of protection, splash-proof
- Integral zero disc
- Red/green LEDs on the housing, for displaying the upper and lower limit value
- Includes 5 MHz 1/4" dual element measuring head

| | |
|--|------------------|
| Art. no. | 46100 100 |
| Brand | ELCOMETER |
| Manufacturer Part Number | MTG2-TXC |
| Min./max. Pulsed-Echo (P-E) measuring range | 0.63-500 mm |
| Resolution of wall thickness | 0.1 mm |
| Gross Weight | 2.040 kg |
| Product Group | 451 |

