

## ToolTower, small with one door, mobile

® RasterPlan

### Application:

For storing and provisioning tools and small parts.

### Version:

- Sturdy frame with base
- With 4 external perforated panels, 10x10 mm square perforation, grid spacing 38 mm, of which 1 panel as lockable door
- With 4 steering rollers, 2 of which with locking devices according to EN 1757-3

### Advantage:

- Square perforations in walls enable the ToolTower to be custom-equipped as per requirements
- Rapid retooling and conversion of accessories possible for changing workplace requirements
- Mobile application possible thanks to steering rollers
- Interior space can also be fully utilised – equipping possible with tool holders, shelving, boxes, CLIP-O-FLEX system (support rails and trays)



<b>Art. no.</b>	<b>50240 272</b>
<b>Width</b>	700 mm
<b>Depth</b>	700 mm
<b>Punched-hole</b>	10 x 10 mm
<b>Number of shelves</b>	1
<b>Height</b>	1260 mm
<b>Design</b>	Mobile
<b>Distance between centre of hole and centre of hole</b>	38 mm
<b>Number of steering rollers</b>	4
<b>Wheel diameter</b>	125 mm
<b>With wheel lock</b>	Yes
<b>With doors</b>	Yes
<b>Lockable</b>	Yes
<b>Lock type</b>	Cylinder lock
<b>Material</b>	Sheet steel
<b>Colour of frame</b>	Gentian blue RAL 5010
<b>Colour of perforated panel</b>	Light grey RAL 7035
<b>Colour of roof</b>	Gentian blue RAL 5010
<b>Surface</b>	Plastic-coated

### EAN-Code

4251142242902