

CAT 6_A S/FTP Patchkabel
CAT 6_A S/FTP Patch Cords

- Außenmantel: LSZH
- Aderquerschnitt: AWG 26/7
- Innenleiter: Kupfer (Cu)
- Schirmung: S/FTP (gesamt geflechtgeschirmt, paarweise foliengeschirmt)
- Transparent Gelb gefärbter Stecker mit Metallschirmung
- Hauben mit Knickschutz, Zugentlastung und Rasthebelschutz
- Steckverbinder: FCC & EN 60603-7-51
- Litzen-Innenleiter: 0,148 +/- 0,005 mm
- Manteldurchmesser: 5,8 +/- 0,3 mm
- Isolierung Litzen-Innenleiter: FO-PE
- Betriebstemperaturbereich: -20 °C bis zu +60 °C
- Flammtest: IEC 60332-1, IEC 61034
- PoE+ kompatibel

- Sheath: LSZH
- Wire cross-section: AWG 26/7
- Conductor: Copper (Cu)
- Shielding: S/FTP (complete braid shielding, pairs foil shielded)
- Transparent yellow colored plug with metal shielding
- Boots with kink protection, strain relief and latch protection
- Connector: FCC & EN 60603-7-51
- Stranded wire: 0.148 +/- 0.005 mm
- Diameter cable jacket: 5.8 +/- 0.3 mm
- Isolation stranded wire: FO-PE
- Operating temperature range: -20 °C up to +60 °C
- Flame retardancy: IEC 60332-1, IEC 61034
- PoE+ compatible



Farbe Color Länge Length	Grau Grey	Blau Blue	Schwarz Black	Grün Green	Rot Red	Gelb Yellow
0,25 m	DK-1644-A-0025 4016032326021	DK-1644-A-0025/B 4016032326892	DK-1644-A-0025/BL 4016032327127	DK-1644-A-0025/G 4016032327158	DK-1644-A-0025/R 4016032327172	DK-1644-A-0025/Y 4016032327202
0,50 m	DK-1644-A-005 4016032327233	DK-1644-A-005/B 4016032327264	DK-1644-A-005/BL 4016032327271	DK-1644-A-005/G 4016032327288	DK-1644-A-005/R 4016032327295	DK-1644-A-005/Y 4016032327301
1,00 m	DK-1644-A-010 4016032327318	DK-1644-A-010/B 4016032327325	DK-1644-A-010/BL 4016032327332	DK-1644-A-010/G 4016032327349	DK-1644-A-010/R 4016032327356	DK-1644-A-010/Y 4016032327363
2,00 m	DK-1644-A-020 4016032327370	DK-1644-A-020/B 4016032327387	DK-1644-A-020/BL 4016032327394	DK-1644-A-020/G 4016032327134	DK-1644-A-020/R 4016032327400	DK-1644-A-020/Y 4016032327417
3,00 m	DK-1644-A-030 4016032327424	DK-1644-A-030/B 4016032327431	DK-1644-A-030/BL 4016032327448	DK-1644-A-030/G 4016032327455	DK-1644-A-030/R 4016032327462	DK-1644-A-030/Y 4016032327479
5,00 m	DK-1644-A-050 4016032327486	DK-1644-A-050/B 4016032327509	DK-1644-A-050/BL 4016032327493	DK-1644-A-050/G 4016032327516	DK-1644-A-050/R 4016032327523	DK-1644-A-050/Y 4016032327530
7,00 m	DK-1644-A-070 4016032327547	DK-1644-A-070/B 4016032327554	DK-1644-A-070/BL 4016032327561	DK-1644-A-070/G 4016032327578	DK-1644-A-070/R 4016032327585	DK-1644-A-070/Y 4016032327592
10,00 m	DK-1644-A-100 4016032327615	DK-1644-A-100/B 4016032327622	DK-1644-A-100/BL 4016032327639	DK-1644-A-100/G 4016032327646	DK-1644-A-100/R 4016032327653	DK-1644-A-100/Y 4016032327660
15,00 m	DK-1644-A-150 4016032327677	DK-1644-A-150/B	DK-1644-A-150/BL	DK-1644-A-150/G	DK-1644-A-150/R	DK-1644-A-150/Y
20,00 m	DK-1644-A-200 4016032327738	DK-1644-A-200/B	DK-1644-A-200/BL	DK-1644-A-200/G	DK-1644-A-200/R	DK-1644-A-200/Y
25,00 m	DK-1644-A-250 4016032327790	DK-1644-A-250/B	DK-1644-A-250/BL	DK-1644-A-250/G	DK-1644-A-250/R	DK-1644-A-250/Y
30,00 m	DK-1644-A-300 4016032327851	DK-1644-A-300/B	DK-1644-A-300/BL	DK-1644-A-300/G	DK-1644-A-300/R	DK-1644-A-300/Y

Gelb hinterlegt = Ware ab Lager verfügbar
Yellow highlighted = Available from stock

Neutral hinterlegt = Ware auf Anfrage erhältlich
not highlighted = Available on request

