

SVS ECO LED VALVE PLUG FORM A 18MM LED VDR 24V


2+PE field-wireable M20x1,5


Form A (18 mm)
24 V AC/DC with LED and VDR
M20 × 1.5 mm
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration



stay connected

Height: 31 mm

Product may differ from Image

Approvals



Form

29005

Technical Data

Contact figure	Cable outlet can be turned in 90° steps
Operating voltage	24 V AC/DC ±10 %
Operating current per contact	max. 1.5 A
Compression gland	M20 × 1.5 mm
Connection cross section	0.5...1.5 mm ²
Sealing range (cable diameter)	8...10 mm
Protection	IP65 inserted and tightened
Locking of ports	M3 (recommended torque 0.4 Nm)

General data

Temperature range	-25...+60 °C
-------------------	--------------

Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1