

PNEUMATIC GREASE GUN - CONTINUOUS OPERATION



Description

Pneumatically operated gun . Max. discharge pressure: 400 bars . Distributed volume per pulse: 0.8 cm³ . European type compressed air coupling (26) . Supplied with straight rigid coupling . Intended for continuous operation Standard: DIN 1284

Strong points

Performance unaltered after 40,000 cycles



Characteristics

Ref.	EAN	Capacity ml	Weight kg	Dimensions (LxWxH) mm	Burst pressure bar
842853	3660338062032	500	2,1	400x170x75	1200