

INDUSTRIAL TRAILERS



IT561C

CE marked & plated
 Platforms of exterior grade plywood construction
 Ball bearing turntable design assuring easy turning
 even when fully laden

Safety Features Include:

A 'stop' prevents the drawbar dropping below 230mm from the ground
 A 'lock' holds the drawbar vertically

Heavy king pins & spring loaded retaining ball in the rear coupling pin ensure safe towing & eliminates self-releasing
 Wire mesh superstructure, many more sizes & options are available - call for details

Description	Model
Friction Parking Brake - Can be fitted to all new trucks. Operated by a foot pedal at the rear of the platform	IT709A

Description	Model
Towing Hitch - When several trailers are to be used in a train. A rear towing hitch can be fitted to all new trucks	IT710A

Load Capacity	Platform Size mm	Platform Height mm	Wheels 4 x Roller Bearing	Without Sides & Ends		With Sides & Ends (300mm Deep)	
				Weight	Model	Weight	Model
1000 kg	2000 x 1000	505	400mm Pneumatic	110 kg	IT541C	143 kg	IT561C
			400mm Cushion	138 kg	IT541M	171 kg	IT561M