






Balloon/storage container 60 L without scale with UV protection, natural-coloured



Description:

Carboys 60 litres, without scale, natural-coloured, extra-thick walls, made of fracture-proof polyethylene

- large opening (50 mm diameter) allows easy filling, emptying and cleaning
- captive screw cap
- useful as settling bottle
- resistant to greases, resins, alkalis, oils and acids
- UV protection for long life
- opening sealed with screw plug for screwing in spigots and corner valves (wide thread 22 mm)
- on request: Custom-made product without screw plug opening, print, labelling, individual scales and colours possible
- separate accessories: Spigots (art. no. 550100 + 560100), corner valves (art. no. 520100 + 520700)
- Replacement parts: Carrying handle, screw cap (diameter 65 mm) and plug set consisting of screw caps and 2 seals
- food-safe, resistant to temperature: -20°C to +70°C and free from bisphenol A (BPA)
- w = inside diameter of filling opening = 50 mm / a = outside thread diameter = 65 mm
- Diameter d=350 mm / height h=830 mm

Information:

Article

Articlenumber	823600
GTIN	4007228823608
Customs tariff	39233090
Packaging Unit (PU)	1

Colour	natural
Volume in l	60
Weight (kg)	2,71
T x B x H (mm)	350 x 350 x 830

Outer packaging

Content in pieces	1
L x B x H (mm)	1180 x 780 x 1065

Gross weight unit (kg)	2,71
------------------------	-------------

Pallet

Number of boxes	2
Number of layers	2
L x B x H (m)	1,2 x 0,8 x 2,28

Carton per layer	1
Weight (kg)	25,42