

## Micrometer

Narrow measuring surfaces

Mitutoyo

### Application:

For measuring narrow external recesses.

### Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces or hardened blades
- Friction coupling for consistent, repeatable measuring force
- Non-rotating measuring spindle

### Advantage:

- Accesses hard-to-reach measuring points

### Delivery:

Includes box, adjustment wrench



<b>Art. no.</b>	<b>32116 552</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	122-116-10
<b>Min./max. length measuring range</b>	275-300 mm
<b>Vernier scale</b>	0.01 mm
<b>Measuring surface depth</b>	6.5 mm
<b>Measuring spindle increments</b>	0.5 mm
<b>Bracket depth</b>	181 mm
<b>Measuring surface width x Measuring surface depth</b>	0.75 x 6.5 mm
<b>Spindle clamping</b>	No
<b>Error limit</b>	6 µm
<b>Display</b>	Nonius
<b>Min./max. measurement force</b>	3-8 N
<b>Calibration Group</b>	D
<b>Gross Weight</b>	2.020 kg
<b>Product Group</b>	3MA

### EAN

4946368847443