

Pneumatic impact wrench RRI-2100M



Execution:

- Motor housing made of composite
- Air outlet through handle
- Rotating air connection
- Adjustable power, two positions
- Left/right switch on the trigger for one-hand operation
- Two-stage trigger for controlled screw-in

Advantage:

- Compact and lightweight
- Mechoneer impact mechanism



Art. no.	75066 232
Brand	RED ROOSTER
Manufacturer Part Number	RRI-2100M
Model	RRI-2100M
Suitable for screw	M20
Max. tightening torque	1000 Nm
Max. idle speed	7500 rpm
Air consumption	12 l/s
Tool holding device	1/2-inch external square
Hammer mechanism system	Twin hammer mechanism
Inner hose diameter	10 mm
Sound-pressure level	88 dB
Weight	2 kg
With right/left-hand rotation	Yes
Gross Weight	2.080 kg
Product Group	7AE

EAN

8717981400799