



SPECIFICATION :
 .CURRENT RATING : 1 AMP.
 .INSULATOR RESISTANCE : 1000 MΩ MIN. (AT 500 V DC)
 .DIELECTRIC WITHSTANDING VOLTAGE : AC 500 V MIN. (FOR 1 MINUTE)
 .OPERATING TEMPERATURE : -55°C TO 105°C
 .CONTACT RESISTANCE : 15mΩ MAX.
 .INSULATOR MATERIAL : PBT WITH GLASS-FIBER REINFORCED UL 94V-0
 .CONTACT MATERIAL : BRASS
 .CONTACT PLATING : GOLD OVER NICKEL
 .WIRE SIZE : AWG 26 & 28 STRANDED , 1.27mm CONDUCTOR CENTRE FLAT CABLE



37	63.50(2.500)	69.40(2.732)	49.86/(1.963)	47.09/(1.854)	54.60/(2.150)	57.10/(2.248)
25	47.04(1.852)	53.09(2.090)	33.24/(1.309)	30.47/(1.200)	38.14/(1.502)	40.90/(1.610)
15	33.32(1.312)	39.10(1.539)	19.39/(.763)	16.62/(.654)	24.00/(.945)	26.60/(1.047)
9	24.99/(.984)	30.80(1.212)	11.08/(.436)	8.31/(.327)	16.10/(.634)	18.60/(.732)
NO. OF POSITIONS	±0.13 A (.005)	±0.25 B (.010)	±0.13 C (.005)	±0.13 D (.005)	±0.25 E (.010)	±0.25 F (.010)

	55.45/(2.183)	59.08/(2.326)	60.73/(2.391)
	38.96/(1.534)	42.52/(1.674)	44.27/(1.743)
	25.25/(.994)	28.80/(1.134)	30.53/(1.202)
	16.92/(.666)	20.47/(.805)	22.20/(.874)
C	±0.25 (.010)	±0.13/(.005) REAR MOUNTING	±0.13/(.005) FRONT MOUNTING

ORDER INFORMATION

C0580 — CONTACT NO: CONTACT TYPE: BODY OPTION: MOUNTING OPTION: CONTACT PLATING: INSULATOR COLOR: **RoHS Compliant**

09, 15, 25, 37 M : Male A : Metal Shell W/D S/R B : Metal Shell W/Metal S/R C : Metal Shell W/Plastic S/R D : Plastic Shell W/D S/R E : Plastic Shell W/Metal S/R F : Plastic Shell W/Plastic S/R

A : Through Hole B : Thread Insert 4-40 UNC C : Thread Insert M3 S : Selective Gold G : Gold Flash A : Gold 50μ B : Gold 10μ C : Gold 15μ D : Gold 30μ

FILL IT WITH '0' RoHS Compliant

玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

UNIT		SCALE		PART NAME	
MM				D-SUB IDC TYPE MALE	
APPD.	CKD.	TOLERANCE	PART NO.	REV.	
			C0580-XXMXXX0R	A	

制表日: 2006/02/13

DRAWING. APPROVED
John