

**CD-BO 80X120 8/12 GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

Type	CD-BO 80X120 8/12 GY
Order No.	<a href="#">2588920000</a>
Version	Cable duct, 80 mm x 120 mm, 8.00 mm x 12.00 mm, 2000 mm
GTIN (EAN)	4050118602890
Qty.	16 m

**CD-BO 80X120 8/12 GY**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	2,000 mm	Length (inches)	78.74 inch
Width	120 mm	Width (inches)	4.724 inch
Height	80 mm	Height (inches)	3.15 inch
Net weight	1,219 g		

**General information**

Colour	grey	Cover	Yes
Flexible wiring duct	No	Halogen	Yes
Material	PVC	Non-tracking	Yes
Slit gap	12 mm	Slit width	8 mm
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	10,770 mm <sup>2</sup>	Version of side panel	slotted

**Classifications**

ETIM 6.0	EC000012	eClass 6.2	27-40-07-03
eClass 9.1	27-40-07-03		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data [STEP](#)

**CD-BO 80X120 8/12 GY**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Drawings**

