



PLUG-IN RELAY, 3 CO CONTACTS, 24V DC, 10A,
WIDTH 22.5MM

General technical data:

| | | |
|---|---|------------|
| Type of voltage | | DC |
| Control supply voltage | | |
| <ul style="list-style-type: none"> • for DC Rated value <ul style="list-style-type: none"> — minimum — maximum | V | 24 |
| | V | 24 |
| Number of NC contacts for auxiliary contacts | | 0 |
| Number of NO contacts for auxiliary contacts | | 0 |
| Number of CO contacts for auxiliary contacts | | 3 |
| Operating current of the auxiliary contacts | | |
| <ul style="list-style-type: none"> • at DC-13 <ul style="list-style-type: none"> — at 24 V • at AC-15 <ul style="list-style-type: none"> — at 230 V | A | 8 |
| | A | 5 |
| Design of the switching function positively driven | | No |
| Switching behavior | | monostable |

Mechanical data:

| | | |
|--|----|----------------------|
| Type of electrical connection | | screw-type terminals |
| Design of the relay operating mechanism | | poled |
| Product component Plug-in socket | | No |
| Width | mm | 22.5 |
| Height | mm | 28 |
| Depth | mm | 35 |

Certificates/ approvals:



[Declaration of
Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZX:PT370024>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZX:PT370024>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZX:PT370024&lang=en

last modified:

15.01.2015