


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2011956000](#)
Status: **Active**
Overview: [Spot-On Wire-to-Board Connector System](#)
Description: [Spot-On Crimp Terminal, Female, Matte Tin \(Sn\) Plating, 22-26 AWG](#)

Documents:

Drawing (PDF)	Product Specification 2012000000-PS-000 (PDF)
Product Specification 2011960000-A00 (PDF)	Packaging Specification 2011959200-200 (PDF)
Product Specification 2011960000-A01 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 2011960000-PS-000 (PDF)	



General

Product Family	Crimp Terminals
Series	201195
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	Spot-On Wire-to-Board Connector System
Product Name	Spot-On
UPC	191128047456

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	40.770/mg
Packaging Type	Reel
Plating min - Mating	0.700µm
Plating min - Termination	0.700µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.25-1.60mm
Wire Size AWG	22, 24, 26
Wire Size mm ²	0.126-0.34

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Crimp Specification	2011956000-C00
Packaging Specification	2011959200-200
Product Specification	2011960000-A00, 2011960000-A01, 2011960000-PS-000, 2012000000-PS-000
Sales Drawing	2011956000-000

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201195 Series](#)

Use With

Spot-On Receptacle Housing [201196](#) ,
[201200](#)