

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0731010120](#)
Status: **Active**
Overview: [BNC Miniature RF Connectors and Cable Assemblies](#)
Description: 75 Ohms, BNC Right-Angle PCB Bulkhead Jack Receptacle with Board Locks, Low Profile, Tray

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E107635

General

Product Family RF/Coax Connectors
 Series [73101](#)
 Comments Low Profile
 Overview [BNC Miniature RF Connectors and Cable Assemblies](#)
 Product Name BNC
 Style PCB
 Type Miniature
 UPC 800753680296
 Wire/Cable Type N/A

Physical

Flammability 94V-2
 Gender Jack
 Keying to Mating Part None
 Net Weight 16.575/g
 Orientation Right Angle
 PCB Mounting Through Hole
 PCB Thickness - Recommended 3.20mm
 Packaging Type Tray
 Panel Mount Yes
 Panel Mount Method Bulkhead
 Reverse Polar No

Electrical

Frequency 2 GHz
 Impedance 75Ω

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
 Lead-free Process Capability WAVE
 Max. Cycles at Max. Process Temperature 001
 Process Temperature max. C 245

Material Info

Reference - Drawing Numbers

Sales Drawing SD-73101-0120



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Prop65

PropRisk

PropRisk

PropRisk

PropSub

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Duty-To-Declare

Cancer

Developmental toxicity

Reproductive toxicity

Lead and its
 compounds

Not Contained

Search Parts in this Series

[73101](#) Series