# Cat6 Patch Cable

multicomp PRO

RoHS Compliant

Specifications

Connector to Connector : RJ45 Plug to RJ45 Plug
LAN Category : Cat6

Diagram

FIGURE_1

No.	Item	Description	Qty.
1	Category 6 UTP Cable	#24X4P+Jacket: PVC, O.D= 6.2±0.2mm	1 PC.
2	8P8C Modular Plug	Contact: Copper Alloy 50µ″, Gold Plated Insulator: Polycarbonate, UL94V-2; Colour: Natural Insert Bar: UL94V-2, Colour: Natural	2 Set
3	PVC Boot	PVC, Shore A: 75±3, Cable Range: 6.86mm	2 PCs.

SEC. A-A

J1	Wire Colour		J2
8	Brown	Twisted Pair	8
7	White/Brown		7
5	White/Blue	Twisted Pair	5
4	Blue		4
6	Green	Twisted Pair	6
3	White/Green		3
2	Orange	Twisted Pair	2
1	White/Orange		1

Dimensions : Millimetres

multicomp PRO

30/04/20   V1.0

Cat6 Patch Cable

multicompPRO

Specification Table

Part Number	Colour	Dimension "L"
SPC23203	Black	304.8 ±12.7mm (1′ ±0.5″)
SPC23204	Blue	
SPC23205	Grey	
SPC23206	White	
SPC23207	Yellow	
SPC23208	Black	914.4 ±25.4mm (3′ ±1″)
SPC23209	Blue	
SPC23210	Grey	
SPC23211	White	
SPC23212	Yellow	
SPC23213	Black	1524 ±25.4mm (5′ ±1″)
SPC23214	Blue	
SPC23215	Grey	
SPC23216	White	
SPC23217	Yellow	
SPC23218	Black	2133.6 ±25.4mm (7′ ±1″)
SPC23219	Blue	
SPC23220	Grey	
SPC23221	White	
SPC23222	Yellow	

Part Number	Colour	Dimension "L"
SPC23223	Black	3048 ±38.1mm (10′ ±1.5″)
SPC23224	Blue	
SPC23225	Grey	
SPC23226	White	
SPC23227	Yellow	
SPC23228	Black	4267.2 ±38.1mm (14′ ±1.5″)
SPC23229	Blue	
SPC23230	Grey	
SPC23231	White	
SPC23232	Yellow	
SPC23233	Black	6096 ±50.8mm (20′ ±2″)
SPC23234	Blue	
SPC23235	Grey	
SPC23238	White	
SPC23237	Yellow	
SPC23238	Black	7620 ±50.8mm (25′ ±2″)
SPC23239	Blue	
SPC23240	Grey	
SPC23241	White	
SPC23242	Yellow	

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicompPRO