

Electronic 3-point quick internal micrometer set

IP67



Application:

For measuring through-bores and blind bores (from \varnothing 12.5 mm) and short centring shoulders in series production.

Execution:

- Self-centring and self-aligning
- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Max./min. value memory
- HOLD function
- Preset function
- Tolerance function

Advantage:

- Pistol grip for quick measurements using retractable lever

Delivery:

1 measuring element, measuring heads with setting rings, battery (1 x 3 V lithium type CR 2032)



| | |
|---------------------------------------------------|---------------------|
| Art. no. | 31919 530 |
| Brand | SYLVAC |
| Manufacturer Part Number | 955.6106 |
| Min./max. length measuring range | 50-100 mm |
| Measuring depth | 80/100 mm |
| Error limit | 4 μ m |
| Data transmission type | Bluetooth/Proximity |
| Digit increment | 0.001 mm |
| IP protection class | IP 67 |
| Adjusting ring diameter | 80 mm, 65 mm |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 3V CR2032 Lithium |
| DIN | 863 |
| Gross Weight | 7.165 kg |
| Product Group | 317 |

EAN

764012502875 1