

## PVC workplace mats

Diamond plate structure, height 9 mm

### Application:

Ideal for dry workstations and light- to medium-duty applications.

### Execution:

- Single-layer, ergonomic PVC mat with non-slip diamond plate surface
- Non-slip and impact resistant, insulates against cold and protects the industrial floor
- R10 slip resistance in accordance with EN 13552
- Fire protection class B2 according to DIN 54332/DIN 4102
- Weight approx. 3.5 kg/m<sup>2</sup>
- Ref. no. 164-167: with yellow safety marking strips on sides

### Advantage:

- Relieves the back and leg muscles and prevents premature fatigue during extended periods of standing
- Increases general safety underfoot
- Easy to cut to the requested dimensions and shape

### Delivery:

Mats delivered with bevelled edges, even if cut to size



<b>Art. no.</b>	<b>50225 160</b>
<b>Manufacturer Part Number</b>	DAF010001
<b>Surface structure</b>	Stud plate / closed
<b>Material</b>	PVC - Polyvinyl chloride
<b>Length</b>	900 mm
<b>Width</b>	600 mm
<b>Material thickness</b>	9 mm
<b>Mat design</b>	Individual mat
<b>Min. temperature resistance</b>	0 °C
<b>Max. temperature resistance</b>	60 °C
<b>Suitable for wet areas</b>	No
<b>Antistatic</b>	No
<b>Anti-fatigue</b>	Yes
<b>Non-slip</b>	Yes
<b>Compliant with REACH</b>	Yes
<b>Colour</b>	Black
<b>Gross Weight</b>	2.000 kg
<b>Product Group</b>	5AD

### EAN

5060103530519