



TUV T5

TUV 22T5 HO G5

TUV T5 lamps are single- or double-ended UV-C 253.7 nm emitting lamps. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

Product data


General Information		Mechanical and Housing	
Cap-Base	G5	Bulb Shape	T5 [16 mm (T5)]
Useful Life (Nom)	9,000 hour(s)		
Light Technical		Approval and Application	
Color Code	TUV	Mercury (Hg) Content (Nom)	5.5 mg
Color Designation	- [Not Specified]		
Depreciation at Useful Lifetime	20 %	UV	
		UV-C Radiation at 100 hr	14.8 W
Operating and Electrical		Product Data	
Power Consumption	48 W	Full product code	871951443888000
Lamp Current (Nom)	0.8 A	Order product name	TUV 22T5 HO G5
Voltage (Nom)	60 V	Order code	928007404099
Voltage (Nom)	60 V	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	40

TUV T5

Material Nr. (12NC)	928007404099
Full product name	TUV 22T5 HO G5
EAN/UPC - Case	8719514438880

EAN/UPC - Product/Case	8719514438880
------------------------	---------------

Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 22T5 HO G5	16 mm	531.1 mm	516.9 mm

