

# NYS325

5 pole DIN chassis connector, silver plated contacts



## Article Variations

Article Name	Details	Packaging
NYS325		

## Technical Information

### Product

<b>Title</b>	NYS325
--------------	--------

### Electrical

<b>Contact Resistance</b>	<10 mΩ
<b>Insulation Resistance</b>	>1000 MΩ(Initial)
<b>Dielectric Strength</b>	500V dc
<b>Rated Voltage</b>	50 VAC

### Mechanical

<b>Insertion Force</b>	≤40N
<b>Withdrawal Force</b>	>5.5N
<b>Lifetime</b>	>1000 Mating Cycles

### Material

<b>Housing</b>	Aluminum
<b>Shield</b>	Bronze
<b>Rivet</b>	Brass
<b>5 Pin Insulator</b>	PA6+30%GF
<b>Jack</b>	Bronze
<b>Housing</b>	Nickel Plating
<b>Shield</b>	Silver Plating
<b>Jack</b>	Silver Plating