


Crimp Terminal, Socket



FEATURES:

Fully-insulated nylon
receptacles
Double crimp
Funnel entry



SPECIFICATION:

Cross-section	1.5...2.5 mm ²
Colour	Blue
Diameter	3.9 mm
Material	Brass
Insulation material	Nylon
Surface material	Tin-plated
Thickness	0.4 mm
Temperature range	max. +105 °C
Length	24 mm
Width	4.65 mm

Art. Nr.

RND 465-00589