

MEN POWER SUPPLY 1/2-PHASE, SMOOTHED


IN: 230/400+/-15VAC OUT: :24V/5ADC


Current: 5 A
Output rating: 120 W
with MES DIN-rail adapter

This power supply units meet the (EN 61000-3-2) standard for harmonic current.

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Input voltage	230/400 ±15 V AC
Input current	0.97 A (230 V AC); 0.56 A (400 V AC)
Input fuse (external)	1.6 AT (230 V AC); 1.0 AT (400 V AC)
Frequency	50...60 Hz

General data

Standards	(EN 61558-2-6), (EN 62041 category I), (EN 55011 B), (EN 61000-3-2)
Mounting method	DIN-rail mountable TH35-15 (EN 60715) or for key-hole mounting
Dimensions H × W × D	95× 96×136 mm
Fixing centers a × b × c	75×84×5.8 mm
Temperature range	-20...+60 °C, no condensation

Output

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 5 A (230 V AC); 6 A (400 V AC)
Ripple	max. 5 %rms
Output fuse	10 A (automotive fuse FKS)
Output filter	LED, VDR and smoothing capacitor

Commercial data

country of origin	CZ
customs tariff number	85044090
minimum order quantity	1