

## Product information

# 95 62 160

## Wire Rope Cutter

Also for high-strength wire rope



- For high-strength wire ropes up to Ø 4 mm and cables up to Ø 6 mm: noticeably light, high-precision cutting thanks to unique, patent-pending joint design
- Compact size, low weight, high performance level
- Made for intensive use: particularly durable and light at only 172 g
- For wire rope with Ø 4.00 / 1960 Nmm<sup>2</sup>
- Compact, light and powerful
- Up to 30 % less physical effort compared to wire rope cutters of the same length
- Double-mounted box joint design for high level of stability
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Convenient work thanks to opening spring
- Secured by locking device during transport
- Ball bearing steel

MM

General	
Article No.	95 62 160
EAN	4003773082354
Shears	burnished
Head	burnished
Handles	with multi-component grips
Weight	175 g
Dimensions	160 x 61 x 21 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-stranded (diameter)	Ø 6.0 mm
Cutting capacities wire rope (diameter)	Ø 4.0 mm

*technical change and errors excepted*



Compact at 160 mm but nevertheless more powerful than many larger wire rope cutters

