


PIN OUT



SHELL ———— SHELL

NOTE:

- 1.OPEN/SHORT/INTERMITTENCE:100%.
- 2.CONDUCTIVE RESISTANCE:2Ω (MAX)
- 3.RoHS & REACH Compliant

| ⑥ | THUMB SCREW | NICKEL PLATED#4-40*15 | 2 | PCS |
|-----|-------------|---|------|------|
| ⑤ | THUMB NUT | NICKEL PLATED#4-40 | 2 | PCS |
| ④ | MOLDED | 45P BLACK PVC | | G |
| ③ | MOLDED | LD-PE | | G |
| ② | CONNECTOR | USB2.0 A FEMALE NICKEL PLATED | 2 | PCS |
| ① | CABLE | 7/0.127TC*1P+7/0.20TC*2C+AD(1/0.254BC)B(64#/0.12AL-MG) OD:4.8±0.2MM | L | MM |
| NO. | MATERIAL | DESCRIPTION | QTY. | UNIT |

| | | | |
|----------------------|---------------------|---|--|
| Ltemref | Quantity | Title/Name,designation,material,dimension etc | Article No./Reference |
| Designed by ALVIN | Checked by HELEN | Approved by - date 10-09-2019 | File name Date 10-09-2019 Scale FREE |
| ANGLE: | | | USB2.0 Panel Mount A Female/Normal A Female 0.5M |
| UNIT:MM | | | Edition 1 |