

Short-length chucks

ERICKSON system with straight shank

ORION[®]

Application:

For use on NC and CNC machining equipment.

Execution:

- Min. tensile strength at core 800 N/mm.
- Hardened.
- Clamping of drill bits on drill heel possible.
- With adjustable longitudinal stop.
- Collets no. 23326.

Advantage:

- With straight shank - extremely slim version.
- Very good accessibility in confined spaces.

Delivery:

1x ERICKSON short chuck system with cylindrical shank.



Art. no.	23325 305
Brand	ORION
Manufacturer Part Number	23325305
Collet type	DK 30
Shank diameter	12 mm
Min./max. clamping width	1-6.5 mm
Width across flats	13 mm
Outer diameter	14 mm
Shaft length	140 mm
Length of head	36 mm
Min. clamp in depth	43 mm
Max. clamp in depth	105 mm
Gross Weight	0.121 kg
Product Group	218

EAN

4039247 156986