

Electronic pocket vernier callipers

IP40 with data output

ATORN[®]

Application

For measuring external, internal, step and depth dimensions.

Version

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- Auto off
- ABS function
- Keeptronic System
- High-contrast display

Advantage

- Key lock to prevent unintentional adjustment
- Switched on by the ON button or automatically switched on by calliper movement

Delivery

In a case, with battery (1 x 3 V lithium type CR 2032)



| | |
|-----------------------------------------|--------------------|
| Art. no. | 31173 112 |
| Min./max. length measuring range | 0-150 mm |
| Data transmission type | multiCOM |
| IP protection class | IP 40 |
| Length of jaw | 40 mm |
| Digit height | 8.5 mm |
| Length of cross tips | 16 mm |
| Digit increment | 0.01 mm |
| Digit increment in inches | 0.0005 in |
| Depth gauge rod | Round |
| Depth gauge rod thickness | 1.5 mm |
| Type of locating | With locking screw |
| Preset function | Yes |
| Calibration Group | A |
| ISO | 13385-1 |

EAN-Code

4050293393354